

Titanium RF Mesotherapy Injection Gun Machine AC100-240V

Our Product Introduction

Basic Information

- Place of Origin: china
- Brand Name: Mesotherapy Gun
- Certification: ce
- Model Number: Titanium
- Minimum Order Quantity: 1 box
- Packaging Details: box
- Delivery Time: 4-7work days
- Payment Terms: L/C, D/A, D/P, T/T, Western Union
- Supply Ability: 10000 box per week



Product Specification

- Product Name: Vanadium-titanium Water Meso Mesotherapy Gun
- Syringes: 5ml
- Keywords: Wrinkle Removal Moisturizing Whitening Injection
- Size: 23.5*15.5*7.5cm
- Voltage: AC100-240v
- Color: White
- Function: Wrinkle Removal Moisturizing Whitening
- Weight: 675g
- Highlight: **Titanium mesotherapy injection gun, rf mesotherapy machine 675g, mesotherapy injection gun AC100-240v**



More Images



for more products please visit us on hadermal-filler.com

Product Description

Meso Mesotherapy Gun For Wrinkle Removal Moisturizing Whitening Injection

Description:

Vanadium Titanium needle free mesotherapy gun (mesogun) adopts advanced processing technology to make an innovation on the injector. Different from mesotherapy guns that use needles, we use a microchip with multiple pins to deliver nutrition and essentials, which can be reached to subcutaneous layer under high pressures from the pistol.


Main Advantages of the Vanadium Titanium Instrument:


1. Refined product, non-corroding, no metal residual, no sensitivity.
2. Just like beauty instrument, painless, noninvasive, no bleeding .
3. Effective permeability, open the tiny pore and enhance the absorption.
4. Aim at the root of skin problem, the absorption rate is 12 times of the normal beauty product.
5. Whole body can do the treatment.
6. Recover immediately, won't affect your normal life and work.




Main Features

- 1.Simple structure in linear type ,easy in installation and maintenance.
2. Adopting advanced world famous brand components in pneumatic parts ,electric parts and operation parts.
3. High pressure double crank to control the die opening and closing.
- 4.Running in a high automatization and intellectualization,no pollution
- 5.Apply a linker to connect with the air conveyor ,which can directly inline with filling machine.





 **shijiazhuang tiantian technology co.,ltd**

 008619931162089  info@tiantianbike.com  hadermal-filler.com

NO 260 HUANAN ROAD SHIJIAZHUANG CITY HEBEI CHINA